MAKROPLUS® CC 1510/LLDPE

Electroconductive concentrate



MAKROPLUS® CC 1510/LLDPE is an electroconductive concentrate based on LLDPE and highly electroconductive carbon black CHEZACARB® AC.

MAKROPLUS® CC 1510/LLDPE is used in applications where permanent antistatic or electroconductive properties are required (e.g. ESD films, foils, packaging).

| PROPERTY | UNIT | TYPICAL VALUE | TESTING STANDARD |
|---------------------|-------------------|---------------|------------------|
| MFI (190 °C, 10 kg) | g/10 min | 10 | ISO 1133 |
| Density | g/cm ³ | 1.00 | ISO 1183 |
| Volume Resistivity | Ω.cm | 10* | ASTM D257 |
| Tensile Strength | MPa | 14.5 | ISO 527 |
| Elongation at Break | % | 7.5 | ISO 527 |
| Flexural Modulus | MPa | 570 | ISO 178 |

^{*} measured on extruded sheets (thickness 1 mm)

MAKROPLUS® CC 1510/LLDPE can be blended with LDPE, LLDPE, HDPE to achieve optimal electrical conductivity (see the graph below).

MAKROPLUS® CC 1510/LLDPE is suitable for extrusion and injection moulding using common processing equipment.


Carbon black's structure is sensitive to high shearing forces. Too much shear stress during processing can damage the structure of carbon black and reduce its electrical conductivity. Excessive shear forces should therefore be avoided.



MAKROPLUS® CC 1510/LLDPE

Volume Resistivity as a function of Makroplus® CC 1510/LLDPE content

measured on extruded sheets: thickness 1 mm



DRYING

Pre-drying is not necessary before processing. If required, the product should be dried at 75 $^{\circ}$ C for 2–4 hrs.

PROCESSING

EXTRUSION: As a general guide, the recommended melt temperature is 170–200 °C during extrusion. Extrusion temperature should be adapted to the equipment, manufactured product and the concentration of MAKROPLUS® CC 1510/LLDPE.

INJECTION MOULDING:

As a general guide, the recommended temperature is 190–210 $^{\circ}$ C (barrel/nozzle) and 40 $^{\circ}$ C mould temperature. Real processing conditions depend on the machine which is used, injection moulded part and on the concentration of MAKROPLUS® CC 1510/LLDPE.

PACKAGING

MAKROPLUS® CC 1510/LLDPE is supplied as pellets (size 2–4 mm) packed in 25 kg PE bags. Larger quantities can be provided in sacks at the customer's request.

STORAGE

The product should be stored in dry conditions at temperatures below 40 $^{\circ}\text{C}$ and protected from UV light. **MAKROPLUS® CC 1510/LLDPE** can be stored for two years in these conditions.

After two years, the properties of the product should be tested.

SAFETY

MAKROPLUS® CC 1510/LLDPE is not recommended for use in any applications with direct contact with food. Despite the concentrate containing no dangerous substances, the product should be handled according to the general rules for handling chemicals. Before processing, please refer to the Material Safety Data Sheet.

The information in this data sheet indicates the typical values obtained by our company and should not be regarded as a specification. These values do not represent a substitute for testing which should be done by the customer.

This information represents our current knowledge on this product and may be revised as new information becomes available. Since we cannot anticipate every end use of the product, our company cannot offer any warranties in connection with any of the information given above. Nothing listed here may be considered a licence or recommendation to infringe any patent rights. This product is not intended for direct contact with food or drugs or for medical use, which requires permanent implantation in the human body.

